






SPECIFICATION
MATERIAL & FINISHES
 INSULATOR: PBT GLASS FILLED UL94V-0
 CONTACT: BRASS
 SHELL : STEEL
 PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL
 Operation voltage: 250 VAC max.
 Current rating: 3 Amps max.
 Contact resistance: 15 mohms max.
 Insulation resistance: 3000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1000 VAC / minute
 Operating temperature: -55°C TO +105°C



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
 TOLERANCES: $\pm 0.10\text{mm}$

TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	DMSC-25S 母头 直插 车针 全金 铆合锁螺丝 PART. NO. D-DMSC25PF-F001			
L.Y.F	2018-04-07				
UNIT	mm	SCALE	free	REV.	A
FILE NO.	Ckmtw-DMSC-0008				