



RoHS&REACH

ECN NO.	DESCRIPTION	DATE
A-0		2022.3.19



NOTES:


MATERIAL:

1. HOUSING MATERIAL :ABS
2. CONTACT MATERIAL :ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE;
GOLD PLATING OVER NICKEL
3. WIRES :UL 1061 26#

ELECTRICAL/PHYSICAL:

1. VOLTAGE RATING :125 VAC RMS
2. CURRENT RATING :1.5 AMP
3. CONTACT RESISTANCE :30 MILLIOHMS MAX
4. INSULATION RESISTANCE :500 MEGOHMS MIN @500V DC
5. DIELECTRIC WITHSTANDING
RESISTANCE :1000V AC RMS 60Hz. 1MIN
6. DURABILITY :750 CYCLES MIN
7. TEMPERATURE :-40°C/+85°C

PH2.0



623K - X X X X X L:Wire Length

No. Of Positions	No. Of Contacts	Wire Style	Color	Gold Plating
4, 6 or 8	2, 4, 6 or 8	1-24 AWG 2-26 AWG 3-28 AWG	1-Black 2-Gray 3-Other	1-1u" 2-3u" 3-6u" 4-15u" 5-30u" 6-50u"

6	UL 1061 26AWG Wire	2*50mm
5	Contact (Fu")	2pcs
4	PH-T	2pcs
3	Terminal	2pcs
2	PH2.0-2Y (PA66 White)	1pcs
1	623K (ABS Gray)	1pcs
NO.	Specification	Quantity

2	Green	Green
1	Red	Red
623K	PH2.0	
Sequence	Color	

未注公差	设计	X.C.S	比例	1:1
尺寸标注	公差	审核	单位	mm
X.	±0.25	±2.0°	图幅	A4
.X	±0.20	±1.5°	版本	A-0
.XX	±0.15	±1.0°	图数	第1页 共1页
.XXX	±0.10	±0.5°		

恒连电子科技有限公司	EVERCOM ELECTRONIC TECHNOLOGY CO., LTD	http://www.chinarj45.com
产品型号	623K 6P2C灰色 TO PH2.0白色 L50 FU	
产品编号		图纸编号