





NOTES:

- 1.Rating:16V DC
- 1.额定值: 16V DC
- 2.Dielectric Strength:250V (50Hz)AC
- 2.耐电压: 250V (50Hz) AC
- 3.Contact Resistance:≤200mΩ
- 3.接触电阻: ≤200mΩ
- 4.Insulation Resistance:≥50MΩ
- 4.绝缘电阻: ≥50MΩ
- 5.Operating Force:40g±10g
- 5.操作力: 40g±10g
- 6.Life: 20,000 times
- 6.寿命: 20,000 次
- 7.Travel: 6.30±0.10mm
- 7.行程: 6.30±0.10mm

7	Inner slide 内滑片	POM	1	Black 黑色
6	Solder foot 焊锡脚	Brass	3	Ag plating 镀银
5	Base 基座	PPA	1	Black 黑色
4	cover 盖子	Nylon	1	Black 黑色
3	spring 弹簧	SUS	1	
2	reed 簧片	Silver coated copper 覆银铜	1	Ag plating 镀银
1	Press handle 按柄	POM	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP72212
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				