



标“*”为重点检验尺寸

所用物料均符合RoHS标准




MATERIALS AND FINISH

SHELL : STEEL MATERIAL, FRONT NICKEL FINISHED
BACK SHELL TIN FINISHED
INSULATOR : PBT THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, BLACK COLOR
CONTACT MATERIAL : PHOSCU
CONTACT FINISH : FULL GOLD 1u" FINISHED
#4-40 THREADED RIVETS

ELECTRICAL CHARACTERISTICS

CONTACT CURRENT RATING : 5.0 AMPS
CONTACT RESISTANCE : 30 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
TEMPERATURE RATING : -55°C ~ +105°C



东莞市赢海电子有限公司

未注公差 X. ±0.35 X.X ±0.25 X.XX ±0.1 X.XXX ±0.05 X.* ±2° X.X° ±1°	GDP50M-180		比例	1:1
	料号	C970249	设计	Roy
	型号		审核	
	图号		核准	Andy
A/O版		日期	2011.8.09	