








NOTES

MATERIAL

- 1.HOUSING MATERIAL: THERMO PLASTICS UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE T=0.3.
- 3.PLATING: GOLD PLATING ON CONTACT AREA TIN PLATED ON SOLDER AREA, NICKEL PLATD OVER ALL.
- 4.SHIELD: BRASS T=0.20mm WITH NICKEL PLATED.

ELECTRICAL

- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL



- 1.DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.OPERATION: -40℃~+85℃.
- 2.STORAGE: -40℃~+85℃.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

8	/
7	/
6	RX-
5	/
4	/
3	RX+
2	TX-
1	TX+
PIN	说明



PCB LAYOUT

TOL:±0.05

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X':±3°	PART NO. RJ45-1020-8P	TITLE: RJ45 沉板2.8 SMT 有壳左黄右绿		
X.X:±0.25	X.X':±2°		MANUFACTURE DWG		
X.XX:±0.15	X.XX':±1°				
UNITS	mm	DESIGN: Ethan	 SCALE N:A SHEET 1/1		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			