







YELLOW



UP LEFT

GREEN




UP RIGHT

YELLOW





DOWN LEFT

GREEN



DOWN RIGHT



NOTES

MATERIAL

- 1.HOUSING MATERIAL: THERMO PLASTICS UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- 3.PLATING: GOLD FLASH PLATING OVER NICKEL.
- 4.SHIELD: BRASS $T=0.20\text{mm}$ WITH NICKEL PLATED.

ELECTRICAL

- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

PCBLAYOUT
TOL:±0.05

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X':±3"	PART NO. RJ45-4023-64P	TITLE: RJ45 2x4带弹左黄右绿DIP P16.26		
X.X:±0.25	X.X':±2"				
X.XX:±0.15	X.XX':±1"				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1