





Circuit diagram



NO.1	
PART NO	H
A	3.8
B	4.3
H	4.5
D	5.0
F	6.5

NO.2	
PART NO	vigor
3	160±30
4	250±50

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	—	2	Brass(0.20t)	Plating silver	—
④	Contact	—	2	F.Ag/SUS	—	—
③	Base	—	1	NYLON	Black	—
②	Cover	—	1	SPCC	Plating Sn	—
①	Keystoke	—	1	NYLON	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2022.4.9					
CHECKED				TITLE:	TACT SWITCHS		
APPROVALS				PART NO.	K2-1109SW-□□SW-□□		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____		
					SHEET 1 OF 1		

—	A	—	NEW	—	—	—
ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.