







PCB.焊接图
PCB.WELDING DRAWING



NOTES:

- 1.Rating:12VDC 50mA
1.额定值: 12VDC 50mA
- 2.Dielectric Strength:250V AC
2.耐电压: 250V AC
- 3.Contact Resistance:≤100mΩ Max
3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ
4.绝缘电阻: ≥100MΩ
- 5.Operating Force:160±50gf
5.操作力: 160±50gf
- 6.Life: 20,000 times
6.寿命: 20,000 times
- 7.Travel: 0.20±0.10mm
7.行程: 0.20±0.10mm
- 8.Operating Temperature Range: -20℃~80℃
8.工作温度: -20℃~80℃

5	Button 按钮	PPA	1	White 白色
4	Cover plate 盖板	Iron cover plate	1	Copper tin plating 镀铜锡
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Body 本体	PPA	1	Whith Black 白色 黑色
1	card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4						COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3						X.XX ± 0.10		DRAWN BY	FUYUAN	CHECKED BY	COCO	
A2						X.X ± 0.15		DATE	2019	APPROVAL B	ALEN	MODEL NO: TP15011645
A1						X ± 0.25		ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		ANGULAR						Https: www.rocpcu.tw

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission