





标“*”为重点检验尺寸

所用物料均符合RoHS标准



PCB LAYOUT

POS.	A±0.2	B±0.2	C±0.2	D±0.2
15	16.33	24.99	30.81	19.28
26	24.70	33.30	39.20	27.70
44	38.38	47.04	53.04	41.30



MATERIAL:

- 1 INSULATOR:PBT+30% GLASS FIBER(UL94-0).
- 2 CONTACT:BRASS.
- 3 CONTACT PLATED:GOLD FLASH OVER NICKEL.
- 4 SHELL:STEEL NICKEL PLATED.
- 5 CONTACTS:15P,26P,44P,62P.

SPEIFICATION:

- 1 RATING CURRENT:5AMPS.
- 2 INSULATION RESISTANCE:1000MΩ MIN.AT 500V
- 3 DIELECTRIC STRENGTH:500V FOR ONE MINUTE.
- 4 OPERATION TEMPERATURE:-500° TO +105°C

东莞市赢海电子有限公司

未注公差		GHDM15F-180		比例	1:1
X	±0.35	料号	C970237	幅面	A4
XX	±0.25			日期	2011.8.09
XXX	±0.1	型号		审核	
XXX	±0.05	图号		日期	
X* ±2° X* ±1°				核准	Andy
A/O版		图号		日期	2011.8.09