

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.

Housing: PBT+30%G.F UL94V-0, Color: Black

端子: 磷/青铜, 镍底30u"MIN, 表面镀金0.8u"MIN

Contact: Phosphor bronze, 0.8u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V.

Withstanding Voltage: AC 500V.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C

Ordering Information

F185-12 XX A0 A SY E X

NO. OF PINS
PER ROW
2-40P

Contact
Full of Gold

Plating
Semi-gold

INSULATOR
MATERIAL:

PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

B0=0.8u"
B1=1u"
B2=1.5u"
B3=2u"
B4=3u"
B5=5u"
B6=10u"
B7=15u"
B8=20u"
B9=30u"


C PA9T
D LCP

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

客编:

注意
事项

- 带*为重点管控
- 管控接触点镀金0.8u"



				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	+0.25	UNIT		MM			
				X.XX	+0.20	SIZE	A4	DESIGN	杨哲	PART NO.	F185-12XXA0ASYEX
				X.XXX	+0.10						
				Angle	+13°	SHEET	1/1	CHECK		TITLE	2.54排母8.5mm塑高 2*XXP 180度 DIP:3.2 Y型 PBT料 (接触点镀金0.8u)
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	APPROVE	DIM	TOL	PROJ.		APPROVE	Customer No.