








# NOTES:

1. Rating: 12VDC 50mA  
1. 额定值: 12VDC 50mA
2. Dielectric Strength: 100V AC  
2. 耐电压: 100V AC
3. Contact Resistance: ≤ 100mΩ Max  
3. 接触电阻: ≤ 100mΩ
4. Insulation Resistance: ≥ 100MΩ  
4. 绝缘电阻: ≥ 100MΩ
5. Operating Force: 200 ± 50gf  
5. 操作力: 260 ± 50gf
6. Life: 10,000 times  
6. 寿命: 10,000 times
7. Operating Temperature: -10°C to +60°C  
7. 使用温度: -10 to +60°C



|          |                  |                      |           |                  |
|----------|------------------|----------------------|-----------|------------------|
| 5        | Terminal<br>端子   | Brass                | 1         | Ag plating<br>镀银 |
| 4        | 外壳               | SUS                  | 1         |                  |
| 3        | 簧片               | Silver copper<br>复银铜 | 2         | Ag plating<br>镀银 |
| 2        | 按柄               | PA46                 | 1         | Black<br>黑色      |
| 1        | Pedestal<br>基座   | PPA                  | 1         | Black<br>黑色      |
| NO<br>序号 | Part name<br>部件名 | Material<br>材料       | QTY<br>数量 | Remark<br>备注     |

|     |      |          |             |       |
|-----|------|----------|-------------|-------|
| A4  |      |          |             |       |
| A3  |      |          |             |       |
| A2  |      |          |             |       |
| A1  |      |          |             |       |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



## COMMON TOLERANCE

|         |        |
|---------|--------|
| X.XX    | ± 0.10 |
| X.X     | ± 0.15 |
| X       | ± 0.25 |
| ANGULAR | —      |

|                                                                                                                                                           |        |            |      |                       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------------|------|-----------------------|
| UNIT                                                                                                                                                      | MM     | PROJECTED  |      | PRODUCT NAME:         |
| DRAWN BY                                                                                                                                                  | FUYUAN | CHECKED BY | COCO | MODEL NO: TP611120220 |
| DATE                                                                                                                                                      | 2019   | APPROVAL B | ALEN | Https: www.rocpcu.tw  |
| ROCPCU TECHNOLOGY CO.,LTD                                                                                                                                 |        |            |      |                       |
| Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission |        |            |      |                       |