







1: Au 1U" — B: Black O: Orange
2: Au 3U" — G: Green W: White
5: Au 15U"
6: Au 30U"



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B7	DN2
A6	DP1	B6	DP2
A7	DN1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

05	外壳	不锈钢	1	SUS 304 1/2H,T0.30
04	二次Molding件	High temperature thermoplastic	1	UL94 V-0
03	一次Molding件	High temperature thermoplastic	1	UL94 V-0
02	中夹片	SUS301-H T=0.15	1	不电镀
01	端子	C18400-H T=0.20	1set	功能接触区镀金, 焊脚镀镍
序号	品名	材质	用量	备注

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

	DSND		SCALE: N/A	MODEL TYPE: TYPE-C 3.1		
	DWN		VIEW: 	PART NO.: U263-14XN-5XQC11-1		
	CHKD		UNIT: mm/in	DWG NO.: X-U263-14XN-5XQC11-1		
	APPD		SIZE: A4			
XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET 1/1	REVISION A0