






PCB.焊接图  
PCB.WELDING DRAWING




NOTES:

1. Rating voltage: 50mA DV12V
1. 额定电流: 50mA DV12V
2. Contact Resistance:  $\leq 100\text{m}\Omega$  Max
2. 接触电阻:  $\leq 100\text{m}\Omega$
3. Operating Force:  $260 \pm 50\text{gf}$
3. 操作力:  $260 \pm 50\text{gf}$
4. Travel:  $0.25 \pm 0.1\text{mm}$
4. 行程:  $0.25 + 0.1\text{mm}$
5. Insulation Resistance:  $\geq 100\text{M}\Omega$
5. 绝缘电阻:  $\geq 100\text{M}\Omega$
6. Dielectric strength:  $\geq 250\text{VAC}$
6. 介电强度:  $\geq 250\text{VAC}$
7. Life: 200,000 times
7. 寿命: 200,000 次
8. Operating Temperature:  $-20^{\circ}\text{C} \sim 80^{\circ}\text{C}$
8. 使用温度:  $-20^{\circ}\text{C} \sim 80^{\circ}\text{C}$



电路图



|          |                    |                   |           |                           |
|----------|--------------------|-------------------|-----------|---------------------------|
| 5        | Push button<br>按钮  | PPA               | 1         | Black<br>黑色               |
| 4        | Blind flange<br>盖板 | Iron cover platet | 1         | Copper tin plating<br>镀铜锡 |
| 3        | Shrapnel<br>弹片     | SUS               | 1         | Ag plating<br>镀银          |
| 2        | Noumenon<br>本体     | PPA               | 1         | Balck<br>黑色               |
| 1        | Card<br>卡件         | Brass             | 1         | Ag plating<br>镀银          |
| NO<br>序号 | Part name<br>部件名   | Material<br>材料    | QTY<br>数量 | Remark<br>备注              |

|     |      |          |             |                                                                                                                              |                  |         |                           |                                                                                                                                                          |            |                                                                                       |                           |   |  |   |  |   |  |
|-----|------|----------|-------------|------------------------------------------------------------------------------------------------------------------------------|------------------|---------|---------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|------------|---------------------------------------------------------------------------------------|---------------------------|---|--|---|--|---|--|
| A4  |      |          |             | <div><div>台普</div><div>ROCPCU</div></div> | COMMON TOLERANCE |         | UNIT                      | MM                                                                                                                                                       | PROJECTED  |  | PRODUCT NAME:             |   |  |   |  |   |  |
| A3  |      |          |             |                                                                                                                              |                  |         | DRAWN BY                  | FUYUAN                                                                                                                                                   | CHECKED BY | COCO                                                                                  | MODEL NO: TP13012615      |   |  |   |  |   |  |
| A2  |      |          |             |                                                                                                                              | X.XX             | ± 0.10  | DATE                      | 2019                                                                                                                                                     | APPROVAL B | ALEN                                                                                  | Https:      www.rocpcu.tw |   |  |   |  |   |  |
| A1  |      |          |             |                                                                                                                              | X.X              | ± 0.15  | ROCPCU TECHNOLOGY CO.,LTD |                                                                                                                                                          |            |                                                                                       |                           |   |  |   |  |   |  |
|     |      |          |             |                                                                                                                              | X                | ± 0.25  |                           |                                                                                                                                                          |            |                                                                                       |                           |   |  |   |  |   |  |
| REV | DATE | REVISION | DESCRIPTION |                                                                                                                              | ISSUE            | ANGULAR | _____                     | Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission |            |                                                                                       |                           |   |  |   |  |   |  |
|     |      |          |             | A                                                                                                                            |                  | B       |                           | C                                                                                                                                                        |            | D                                                                                     |                           | E |  | F |  | G |  |