

PRODUCT NO.	1
RoHS compliant	2

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical life :1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations

2. PLATING:

GOLD FLASH 1u”(min.) SOLDERAL,
3u” GOLD PLATING ON THE CONTACT AREA,
WITH 50u” NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX T J G E R

【包装方式, T=管装 R=Reel】





【电镀层: F=镀金部 3u” 焊脚部 1.2u” G=镀金部 3u” 焊脚部 3u” R=镀金部 10u” 焊脚部 10u”

【G= 镀全金 S=内镀金(接触部)外镀锡(焊脚部)】


【脚型: S脚 / J脚 / 1脚 / A脚 / Z脚】

【T= 低推贴胶 S= 低推不贴胶 L=长推】


【产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P】



[Schematic]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	3u” Gold
④	Terminal	Brass	1u” Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u” Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED	INSPECTION COPY
LINER	ANGLES
0 ± 0.25	0 ± 2°
1.00 ± 0.15	.0 ± 1°
.000± 0.10	.00± 0.5°
DESIGN	katky
DRAWING	03/20/12
CHECK	
APPRO.	

东莞市广智实业有限公司 DongGuan Kingtek Industrial Co., Ltd.			
TITLE			
BY DSHP SERIES PITCH 1.27mm			
PRODUCT FAMILY DSHP SERIES			
PRAT NO. DSHP08TUGER			
FILE NO.	DSHP08TUGER-A	SIZE	UNIT
SCALE	SHEET	REV.	REV.
A4	mm	2 : 1	10F-1 A