

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

B256-1 14 A0 B M B E 1

NO. OF PINS	Contact Plating	INSULATOR MATERIAL	BACK	PACKING
4~100P	Full of Gold	Semi-gold	Grey 427	PE Bag
A0=0.8u"	B0=0.8U"	B PA6T	E: Grey 413	B Tape & Reel
A1=1u"	B1=1U"	C PA9T	W White	C Tube
A2=1.5u"	B2=1.5U"	D LCP	U Blue	D Tube+CAP
A3=2u"	B3=2U"			E Tray
A4=3u"	B4=3U"			
A5=5u"	B5=5U"			
A6=10u"	B6=10U"			
A7=15u"	B7=15U"			
A8=20u"	B8=20U"			
A9=30u"	B9=30U"			
S1=Ordinary Tin Plated				
S2=Matte Tin Plated				
S3=Tin-plated High-temperature				

RoHS
COMPLIANT

1. 带*为品质重点检验尺寸

注意事项

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	+0.25	UNIT		MM					
				X.XX	+0.20	SIZE		A4	DESIGN	李官淼2022.06.09		PART NO.	B256-114A0BMBE1
A0	2022.06.09	/	新版发行	X.XXX	+0.10	SHEET		1/1	CHECK			TITLE:	2.0简易牛角 14P SMT 黑色 PA6T料 镀普金 L=7.5/6.5(0)/3.8
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	Angle	+3°	PROJ.			APPROVE			Customer No.	
				DIM	TOL								