





PCB Layout

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

技术指标:

- 1、塑件表面应光洁、无毛刺、明显收缩、缺陷、裂纹等现象;
- 2、温度范围: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$
- 3、额定电压: 200V, AC, DC(等效);
- 4、接触电阻: $\leq 30\text{M}\Omega$;
- 5、绝缘电阻: $\geq 500\text{M}\Omega$
- 6、耐压: 1000V, AC/minute.

Poles	PART NO.	Dimension mm		
		A	B	C
2	W-1251M02P-0400	1.25	4.25	7.30
3	W-1251M03P-0400	2.50	5.50	8.55
4	W-1251M04P-0400	3.75	6.75	9.80
5	W-1251M05P-0400	5.00	8.00	11.05
6	W-1251M06P-0400	6.25	9.25	12.30
7	W-1251M07P-0400	7.50	10.50	13.55
8	W-1251M08P-0400	8.75	11.75	14.80
9	W-1251M09P-0400	10.00	13.00	16.05
10	W-1251M10P-0400	11.25	14.25	17.30
11	W-1251M11P-0400	12.50	15.50	18.55
12	W-1251M12P-0400	13.75	16.75	19.80
13	W-1251M13P-0400	15.00	18.00	21.05
14	W-1251M14P-0400	16.25	19.25	22.30
15	W-1251M15P-0400	17.50	20.50	23.55
16	W-1251M16P-0400	18.75	21.75	24.80

3	焊片 Fitting Nail	磷青铜 Phosphor Bronze	2	电镀(镀): 整个表面镀底镍30u"MIN,再镀80u"MIN.
2	端子 Contact	磷青铜 Phosphor Bronze	n×1	电镀(镀): 整个表面镀底镍30u"MIN,再镀80u"MIN.
1	基板 Wafer	PA9T(UL94V-0)	1	本色
NO.	PartName	MATERIAL	QTY	Remark

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 1251SMT-XP 卧贴 PA9T料			
DRAWN: LYF	DATE: 2011-01-13	PART. NO.	W-1251MXXP-0400		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-1251-0033	REV.	A XFR0