

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 灰色.

Housing: PBT+30%G.F UL94V-0, Color: gray

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

E101-1 20 A0 A R G E 1

1. LONG-EARED	NO. OF PINS	Contact	Plating	INSULATOR	BACK	PACKING
2. SHORT-EARED	6-64P	Full Gold	Semi-gold	MATERIAL:	Gray427	PE Bag
		A0=0.8u"	B0=0.8u"	A: PBT	E: Gray413	B: Tape & Reel
		A1=1u"	B1=1u"	B: PA6T	WW: White	C: Tube
		A2=1.5u"	B2=1.5u"	C: PA6T	U: Blue	D: Tube+CAP
		A3=2u"	B3=2u"	D: LCP		E: Tray
		A4=3u"	B4=3u"			
		A5=5u"	B5=5u"			
		A6=10u"	B6=10u"			
		A7=15u"	B7=15u"			
		A8=20u"	B8=20u"			
		A9=30u"	B9=30u"			
		S1=Ordinary Tin Plated				
		S2=Middle Tin Plated				
		S3=Tin-plated High-temperature				

RoHS
COMPLIANT

客编:

注意事项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	李官森2021.11.20	PART NO	E101-120A0ARGE1	
A0	2021.11.20	/	新版发行	X.XXX	±0.10							
				Angle	±3°	SHEET	1/1	CHECK		TITLE	2.54传统牛角 20P 90度 灰色 DIP:3.8 长耳 PBT料 镀普金 108/盒	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.		