


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.06	阿树



NOTE 备注:

1.MATERIAL 材质:

1.1.HOUSING 胶壳: PBT BLACK

1.2.TERMINAL 端子: H62 T=0.18mm
PLATING 电镀: GF Au AND Tin 100u"MIN

1.3.SHELL 外壳: SPCC T=0.30mm
PLATING 电镀: Ni 100u" MIN

2.ELECIRICAL (电气特性):

2.1.THE VOLOAGE&CURRENT,RATE(额定电压和电流):
30V AC, 2.0-3.0A MAX;

2.2.WIIHSTANDING VOLTAGE(耐压强度);
250V AC/ Iminute 漏电流0.5mA Max;

2.3.CONTACT RESISIANCE(导通阻抗):
30mΩ obms Max AT 100mA;

12.4.INSULATE RESISIACE(绝缘阻抗);
100M ohms Min AT 20℃;

3.MECHANICAL (物理特性);

3.1.MATING FORCE(插入力):3.50kgf MAX;

3.2.UNMATING FORCE(拔出力):1.00kgf Min;

3.3.LIPE TEST(寿命测试):5000cyc les min;
200cyc les/hour;

4.SALT SPRAY TEST TIME: 48H

5.符合RoHS, REACH

U216-04XN-1XS82-X

1:Au 1U"
6:Au 30U"

1:SPCC
5:BRASS

B:Black
W:White

1:PBT
2:PA6T
3:PA9T
4:LCP

AuGLAR	±5°		DESIGN	阿树	VIEW: 	MODEL TYPE: USB 2.0		
X.	±0.40		CHECKED		UNIT: mm/in	PART NO.: U216—04XN—1XS82—X		
X.x	±0.30		APPROVED		SIZE: A4	DWG NO.:		
X.xx	±0.20							
X.xxx	±0.15							
UNSPECIFIED TOLERAUCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
www.xk-dg.cn						N/A	1/1	A1