








P.C.B LAYOUT



SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 2P3T
4. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
5. Operating Force: $200\pm 80\text{gf}$, $300\pm 100\text{gf}$, $350\pm 100\text{gf}$, $450\pm 100\text{gf}$
6. Life test: 10,000 cycles

KNOB $X=2, 3, 4\text{mm}$ TERMINAL $Z=6.9, 7.5, 10.5\text{mm}$

					TOLERANCE UNLESS SPECIFIED						
					UP TO 5mm: ±0.1	ANGULAR	A0	2017.04.26	首次发行		GYW
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY APPD
4	MK22D10 CONTACT/SPRING	PBS	2	Ag CLAD/NATURAL	TITLE:MINI SLIDE SWITCH			UNIT : MM	ROHS	DWN	
3	MK23D38 KNOB	PA66/PA6T	1	BLACK/WHITE	MODEL: MK-23D20G2-B弹线			SCALE: 6:1	COMPLIANT	CHK'D	
2	MK23D38 COVER	SUS	1	WASHING	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD		
1	MK23D38 CASE	PA6T/BRASS	1	BLACK/Ag PLATED							
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:  		REV :A0