






ROHS

Http://www.krhro.com



|      |       |      |      |
|------|-------|------|------|
| PIN  | ø1.65 | ø2.0 | ø2.5 |
| APPD | 165   | 20   | 25   |

Rating: 8A 24V DC  
 Contact Resistance: 100 mΩ Max.  
 Operating temperature: -20℃~70℃  
 Operating force: 3~20N  
 Operating Life: 5,000 cycles

| ④    | PIN       | —       | 1    | Brass           | Au Plating | —      |
|------|-----------|---------|------|-----------------|------------|--------|
| ③    | Cover     | —       | 1    | SUS             | Ag Plating | —      |
| ②    | Terminal  | —       | 3    | Phosphor bronze | Ag Plating | —      |
| ①    | Housing   | —       | 1    | PPA             | Black      | —      |
| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL        | FINISHING  | REMARK |

|                |       |        |            |             |                                                                                       |       |                                                                                       |  |
|----------------|-------|--------|------------|-------------|---------------------------------------------------------------------------------------|-------|---------------------------------------------------------------------------------------|--|
| APPROVALS      |       |        | DATE       |             |  |       |                                                                                       |  |
| DRAWN          |       | LIUCAN | 2021.11.16 |             |                                                                                       |       |                                                                                       |  |
| CHECKED        |       |        |            |             | TITLE:                                                                                |       | DC JACKS                                                                              |  |
| APPROVALS      |       |        |            |             | PART NO.                                                                              |       | DC-028C                                                                               |  |
| TOLERANCES ARE | 30~以上 | ±0.30  | ANGLE      | UNIT: mm    | SCALE: 1:1                                                                            | PROJ: |  |  |
|                | 10~30 | ±0.20  |            |             |                                                                                       |       |                                                                                       |  |
|                | 5~10  | ±0.15  |            |             |                                                                                       |       |                                                                                       |  |
|                | ~ 5   | ±0.10  |            |             |                                                                                       |       |                                                                                       |  |
|                |       |        | ±2'        | DRAWING NO. |                                                                                       |       | SHEET 1 OF 1                                                                          |  |

| —       | A    | —     | NEW          | —       | —      | —      |
|---------|------|-------|--------------|---------|--------|--------|
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |