




材料及电镀

- 1. 塑件主体：PA66，
- 2. 焊 针：黄铜，镀镍

电气性能

额定电压：300V
额定电流：8A
接触电阻：20mΩ（Max）
绝缘电阻：500MΩ\DC1000V
耐 电 压：AC1500V\1Min

机械性能


温度范围：-40℃ ~ +105℃
瞬时温度：+250℃，5秒

2	插针	铜	镀镍	
1	基座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	接线端子
料 号 PART NO	HC-JXDZRC-3.81-7P

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1																						
<table><tr><th>Poles</th><th>Dim</th><th>DimP</th><th>DimL</th></tr><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td><td></td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td><td></td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td><td></td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td><td></td></tr></table>	Poles	Dim	DimP	DimL	2-6P	±0.10	±0.20		7-12P	±0.20	±0.30		13-18P	±0.25	±0.40		19-24P	±0.30	±0.50		单 位 UNIT	MM	制 图 DRAW	AhYe
	Poles	Dim	DimP	DimL																				
	2-6P	±0.10	±0.20																					
7-12P	±0.20	±0.30																						
13-18P	±0.25	±0.40																						
19-24P	±0.30	±0.50																						
	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云																				
	版 本 REV	A	批 准 APPROVE	赵亮亮																				

