

A		B		C		D		E		F		G									
图面产品均符合ROHS标准 “*”为重点尺寸																					
1		2		3		4		5		6		7									
<p>Note:</p> <ol style="list-style-type: none"> <li>1. Impedance : 50 Ω ;</li> <li>2. Frequency Range :0-6 GHz ;</li> <li>3. VSWR : 1.5 Max.</li> </ol>																					
<p><b>BOM 表</b></p>																					
8	弹 垫	2L01-0001G	Φ8.60*1.00 弹簧钢 镀1-3U"金	PCS	1																
7	内齿华司	2F02-0003G	Φ10.2*0.50 C3604 镀1-3U"金	PCS	2																
6	螺 母	2K01-0001G	H8.00*1.75 C3604 镀1-3U"金	PCS	1																
5	推 管	2H02-0007G	Φ2.90*7.00*Φ1.10 C3604 镀1-3U"金	PCS	1																
4	绝缘垫片	2D02-0013	Φ1.80*0.70*Φ0.70 白色铁弗龙	PCS	1																
3	中芯针	2E02-0009G	Φ1.50*11.30*Φ0.80 C3604 镀3U"金	PCS	1																
2	绝缘体	2D01-0209	Φ4.17*11.30*Φ1.30 白色铁弗龙	PCS	1																
1	螺牙主体	2A03-0170G	H8.00*18.90*Φ2.00 C3604 镀1-3U"金	PCS	1																
序号	名 称	料 号	物 料 描 述	单 位	数 量																
<p><b>HJ-Tech 东莞市皇捷通讯科技有限公司</b> 手机: 15015262131 手机: 13714786106</p>																					
<p>品名规格: SMA JACK 13 牙母针 FOR RG-1.13 CABLE</p>																					
<p>公 差</p>		<p>x. ±0.30 x. x. ±0.20 x. xx ±0.10 ANGULAR ±5°</p>				<p>视 图</p>		<p>设 计</p>		<p>L H M</p>		<p>料 号</p>		<p>HJ-9AJL3-060</p>							
		<p>视 图</p>														<p>审 核</p>		<p>日 期</p>		<p>2020-11-05</p>	
<p>A</p>		<p>B</p>		<p>C</p>		<p>D</p>		<p>E</p>		<p>F</p>		<p>G</p>									