



1. Rating voltage: 50mA DC12V
1. 额定电压: 50mA DC12V
2. Contact Resistance: $\leq 100\text{m}\Omega$ Max
2. 接触电阻: $\leq 100\text{m}\Omega$
3. Operating Force: $260\pm 50\text{gf}$
3. 操作力: $260\pm 50\text{gf}$
4. Insulation Resistance: $\geq 100\text{M}\Omega$
4. 绝缘电阻: $\geq 100\text{M}\Omega$
6. Life: 50,000 times
6. 寿命: 50,000 times
7. Travel: $0.20\pm 0.1\text{mm}$
7. 行程: $0.20\pm 0.1\text{mm}$
8. Operating Temperature: $-20^{\circ}\text{C}\sim 80^{\circ}\text{C}$
8. 使用温度: $-20^{\circ}\text{C}\sim 80^{\circ}\text{C}$

5	Push-button 按钮	LCP	1	Black 黑色
4	Blind flange 盖板	Brass	1	Ag plating 镀银
3	Shrapnel 弹片	SUS	2	Ag plating 镀银
2	Noumenon 本体	LCP	1	white 白色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP13322635		
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION		ISSUE	X							± 0.25
					ANGULAR	_____	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission						
	A			B			D		E		F		G