





RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: $\pm 0.10\text{mm}$

TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05

SPECIFICATION
MATERIAL & FINISHES
INSULATOR: PBT GLASS FILLED UL94V-0
CONTACT: BRASS
SHELL : STEEL
PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL
Operation voltage: 250 VAC max.
Current rating: 3 Amps max.
Contact resistance: 15 mohms max.
Insulation resistance: 3000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC / minute
Operating temperature: -55°C TO $+105^{\circ}\text{C}$



APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	DMS-37P 公头 直插 车针 全金 铆合锁螺丝 PART. NO. D-DMSC37PM-F001			
L.YF	2018-04-07				
UNIT	mm	SCALE	free	REV.	A
FILE NO.	Ckmtw-DMSC-0004				