







Schematic(Shorting)



P.C.B layout



⑦	Steel Ball	—	2	Steel	Natural	—
⑥	Spring	—	1	Steel Wire	Natural	—
⑤	Contact Clip	—	2	PBS Strip	Ag Plated	—
④	Terminal	—	8	Brass Strip	Ag Plated	—
③	Base	—	1	Phenolic Resin	Natural	—
②	Frame	—	1	Steel Strip	Ni Plated	—
①	Knob	—	1	POM	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro®		
DRAWN	QIFENG.XU	2013/6/13					
CHECKED					TITLE:	Toggle Switch	
APPROVALS					PART NO.	SS-23E06-G5	
TOLERANCES ARE			30~以下	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
			10~30	±0.20			
			5~10	±0.15			
			~ 5	±0.10			
			±2'	DRAWING NO.	_____		SHEET 1 OF 1