



REV.	ECN NO.	REVISED	DATE

1.MATERIAL:
a.HOUSING:LCP UL94V-0
b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING: Au1u")
SEE ORDERING INFORMATION

2.ELECTRIC:
a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
d.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION
BS-06-B4AA002-R

电池座系列





BS-06系列

SMT 180° TYPE


PLATING:
A-Au1U"
J-Ni100U"~120U"
K-Sn100U"~120U"

MATERIAL:
1A-PBT BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK
5A-PA6T WHITE
5B-PA6T BLACK

工程部
2023-10-10
H. WANG




PCB Layout Diagram
Top View





3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.15mm	Gold Plating and Ni Under-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.15mm	Gold Plating and Ni Under-Plating
1	HOUSING	1	LCP	WHITE
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR





UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2023-10-10
		CHKD	ZhouRuicai	DATE	2023-10-10
		APVD	XueShunyang	DATE	2023-10-10
WEIGHT:		SCALE: 2:1	SIZE: A4	VIEW:	TITLE: BS-2032-6 Au SMT 卷装
SHEET 1 OF 2		UNIT: mm	REV.: A/0	OBJECT: MY	PART NO.: BS-06-B4AA002-R
		DRAW NO.:MY-CP-0014			




产品





6盘



Detail A



出料方向



10空穴


末端留空穴载带

共封装 500 只产品


300MIN

15空穴

前端留空穴载带




Detail A



- 技术要求:
- 圆孔十个孔距距离累计允许公差为 $\pm 0.2\text{mm}$
 - 带长250mm内容许弯曲度1mm
 - 材料厚度以在载带边缘测量为准
 - 所有尺寸定义依循EIA-481-C系准则定义之
 - 材料: 黑色PS T=0.35mm
 - 所有卷轮为灰蓝挖空旋转贴胶卷轮
 - 整模成型长度:10.5M,
 - 非指明公差范围为: $\pm 0.1\text{mm}$; 超过250mm不计算累计误差
 - 型腔外形凡未标明处倒角R为0.2~0.3; 拔模斜度未标注的为 3° 以下

- 包装信息:
- 每卷盘装产品 500 只, 卷盘外侧贴相关标签;
 - 每 6 卷盘放在一个塑料袋中;
 - 每外箱装6盘, 产品总数: 3000 只;
 - 外箱上下用胶纸封成“工”字;
 - 电池座包材BS-2032-6 SMT 卷装 (BS-6-01-R)



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2023-10-10
X :±***	X :±***	CHKD	ZhouRuicai	DATE	2023-10-10
X.X :±***	X.X :±***	APVD	XueShunyong	DATE	2023-10-10
X.XX :±***	X.XX :±***	WEIGHT:	SCALE: 3:1	SIZE: A4	VIEW:
X.XXX :±***	X.XXX :±***	SHEET 2 OF 2	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE: BS-2032-6 Au SMT 卷装	
				PART NO.: BS-06-B4AA002-R	
				DRAW NO.:MY-BD-0005	