


P. C. B. LAYOUT

MATERIAL

Insulator Material: Polyesetr,UL94V-0

Nylon-6T

Contact Material: Phosphor Bronze(C5191)

Contact Plating: Gold flash over Nickel

Color:Black

SPECIFICATION

Current Rate:2Amp

Contact Resistance:20mΩ MAX.at DC 1A

Insulation Resistance:1000MΩ MIN.atDC500V

Dielectirc Strength:AC500V PER minute

Operation Temperature:-40°to+105°

TOLERANCE TABLE	
. 0	±0. 30
. 00	±0. 20
. 000	±0. 05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 220-2SMT-2*14P H=4.3mm 塑宽4.5mm			
DRAWN: LYF	DATE: 2008-04-29	PART. NO.	B-2202N28P-B121		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-220-20015	REV.	A