




F185-12 03 A0 A SY A 3

Temperture Range: -40° C to+105° C



NQ OF PINS PER ROW	Contact	Plating	INSULATOR	PACKING
2-40P	Full Contact Gold	Semi-gold	MATERIAL:	A: PE Bag
	A0=0.8u"	B0=0.8U'	A: PBT	B: Tape & Foil
	A1=1u"	B1=1U'	B: PA6T	C: Tube
	A2=1.5u"	B2=1.5U'	C: PA9T	D: Tube+CAP
	A3=2u"	B3=2U'	D: LCP	E: Tray
	A4=3u"	B4=3U'		
	A5=5u"	B5=5U'		
	A6=10u"	B6=10U'		
	A7=15u"	B7=15U'		
	A8=20u"	B8=20U'		
	A9=30u"	B9=30U'		
	S1=Ordinary Tin Plated			
	S2= Matte Tin Plated			
	S3= Tin-plated High-temperature			

RoHS
COMPLIANT

客编：

注意事项

1. 带*为品质重点检验尺寸

				OPERATION	SCALE	Fit	 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X ±0.25	UNIT		MM		
				X.XX ±0.20	SIZE	A4	DESIGN	李官森 2021.08.16	PART NO
				X.XXX ±0.10					
A0	2021.08.16	/	新版发行	Angle ±3°	SHEET	1/1	CHECK		TITLE
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM TOL	PROJ.		APPROVE		Customer No.
									F185-1203A0ASYA3 2.54排母8.5mm塑高 2*3P 180度 DIP:2.3 Y型 PBT料 镀黄金 1K/袋