








Model No.	DC-044S-20A	DC-044S-25A
PIN	φ2.0	φ2.5

Rating: 3A 30V DC
 Contact Resistance: 30 mΩ Max.
 Operating temperature: -30℃~70℃
 Operating force: 3-30N
 Operating Life: 5,000 cycles

②	Terminal	——	3	Brass	Ag Plating	——
①	Housing	——	1	PPA	Black	——
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE	 hro®		
DRAWN	LIUCAN	2021.5.28				
CHECKED				TITLE:	PHONE JACKES	
APPROVALS				PART NO.		
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm
			10~30	±0.20		
			5~10	±0.15		
			~ 5	±0.10		
			±2'	DRAWING NO.	SCALE: 1:1	PROJ: 
					SHEET 1 OF	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			