








PCB Layout(Pattern side)




NO.1	
PART NO	H
B	4.3
D	5.0
E	6.0
F	6.3

NO.2-NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER

Typical Specifications

- 1.Rating : DC 12V 50mA
- 2.Contact Resistance: $\leq 100\text{m}\Omega$
- 3.Insulation Resistance: $\geq 100\text{m}\Omega$
- 4.Operating Force: $250 \pm 50\text{gf}$
- 5.Life : 30,000 Cycles



Circuit Diagram

⑥	Waterproof pad	—	1	silica gel	Black	—
⑤	Cover	—	1	Brass	Tin Plated	—
④	Keystoke	—	1	PPA	White	—
③	Contact	—	1	F.Ag/SUS	Plating silver	—
②	Base	—	1	PPA	Black	—
①	Terminal	—	2	Brass(0.3t)	Plating silver	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS

DATE

DRAWN

LIUCAN

2021.9.24

CHECKED

TITLE:

TACT SWITCHS

APPROVALS

PART NO.

K2-1845SD-□4SW-□□

TOLERANCES ARE

30~以上	± 0.30	ANGLE
10~30	± 0.20	
5~10	± 0.15	
~ 5	± 0.10	$\pm 2'$

UNIT: mm

SCALE: 1:1

PROJ:

DRAWING NO.

SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.

