








PCB.安装图



电路图

NOTES:

1. Rating: 12VDC 50mA
1. 额定值: 12VDC 50mA
2. Dielectric Strength: 250V AC
2. 耐电压: 250V AC
3. Contact Resistance: ≤100mΩ Max
3. 接触电阻: ≤100mΩ
4. Insulation Resistance: ≥100MΩ
4. 绝缘电阻: ≥100MΩ
5. Working temperature: -40 °C ~ +85 °C
5. 工作温度: -40 °C ~ +85 °C
6. Stroke: 0.50 ± 0.20mm
6. 行程: 0.50 ± 0.20mm
7. Waterproof grade: IP67
7. 防水等级: IP67
8. Operating Force: 160 ± 60gf
8. 操作力: 160 ± 60gf
9. Life: 200,000 times
9. 寿命: 200,000 次

5	Terminal 端子	Barss	1	Ag plating 镀银
4	Pedestal 基座	PA6T	1	
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Button 按钮	Rubber	1	blue 蓝色
1	Cover 盖板	SUS	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4						COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3						X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP14611652
A2						X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		ANGULAR	—					

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission