

Ordering Information

备注(Remark)

1. 材料(MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.

Housing: PBT+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u", 表面镀金0.8u"

Contact: Brass, 0.8u" GOLD PLATING OVER ALL
30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):



额定电流: 3 AMP
Raring Current:3 AMP.

接触阻抗: 20 m Ω MAX.
Contact Resistance:20 m Ω MAX.



绝缘阻抗: 1000 M Ω MIN.
Insulating Resistance:1000 M Ω MIN.

耐电压: AC 500V/分钟.
Withstanding Voltage:AC 500V/Minute.

温度范围: -40° C to+105° C
Temperature Range: -40° C to+105° C



Recommended P. C. B LAYOUT
General Tolerance ± 0.05



HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full of Gold	Plating Semi-gold	INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING: PE Bag, Tape & Reel
15: 1.5mm	2-40P	A0=0, 8u"	B0=0, 8U"	A: PBT		
17: 1.7mm		A1=1u"	B1=1U"	B: PA6T		C Tube
20: 2.0mm		A2=1, 5u"	B2=1, 5U"	C: PA9T		D Tube+CAP
25: 2.54mm		A3=2u"	B3=2U"	D: LCP		E: Tray
30: 3.0mm		A4=3u"	B4=3U"			
		A5=5u"	B5=5U"			
		A6=10u"	B6=10U"			
		A7=15u"	B7=15U"			
		A8=20u"	B8=20U"			
		A9=30u"	B9=30U"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				

RoHS
COMPLIANT

客编：

注意事项

1. 带序号为必检尺寸
2. 带*为重点检验尺寸

				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM	www.yxcon.com		
				X.XX	±0.20	SIZE	A4	DESIGN	伍思远2023.08.18	PART NO.	P125-1203A0AS116A5
A0	2023.08.18	/	新版发行	X.XXX	±0.10						
				Angle	±3°	SHEET	1/1	CHECK		TITLE	2.54排针 2*3P L=11.6/3.0 180度 打内K PBT料 镀金0.8U 1K/袋
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	

Yxcon 东莞市宇熙精密连接器有限公司
www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.