





PRODUCT NO.	1
DSHP03TJGER	RoHS compliant



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	1μ'-3μ' Gold
④	Terminal	Brass	1μ'-2μ' Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	1μ'-3μ' Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED				INSPECTION COPY			
LINER		ANGLES		PROJECTION		TITLE	
0 ± 0.25		0. ± 2°		100 ± 0.15		BY DSHP SERIES PITCH 1.27mm	
1000 ± 0.10		.00 ± 0.5°		DESIGN		PRODUCT FAMILY DSHP SERIES	
DRAWING		kathy		03/20/12		PRAT NO. DSHP03TJGER	
CHECK						FILE NO. DSHP03TJGER-A	
APPRO.						SIZE UNIT SCALE SHEET REV.	
A4		mm		2 : 1		10F-1 A	

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations


2. PLATING:

GOLD FLASH 1u"~2u" SOLDER TAIL, 1u"~3u" GOLD PLATING ON THE CONTACT AREA, WITH 50u" NICKEL UNDERPLATING COVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX I J G E R

- [包装方式: T=管装 R=Reel]
- [电镀层: E=接触部1u"~3u" 焊脚部1~2u" G=接触部3u" 焊脚部3u" F=接触部0u" 焊脚部0u"]
- [G=镀全金 S=内镀金(接触部)外镀锡(焊脚部)]
- [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P]



东莞市广普实业有限公司
Dongguan Kingtek Industrial Co., Ltd.