




- 8.使用温度: -20 to +70℃



5	Terminal 端子	Brass	3	Ag plating 镀银
4	Reed 簧片	Phosphor bronze 磷青铜	1	silvery white 银白色
3	Hull 外壳	Brass	1	silvery white 银白色
2	Pedestal 基座	LCP	1	Black 黑色
1	Hand shank 手柄	PA46	4	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:				
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP612221220				
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD								
					X	± 0.25									
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission							
				A		B	C		D		E		F		G