





A-A



B-B



C-C



NOTES:

1. Material: Brass, T=0.20mm
2. Finish: Nickel 30u" Min. Over All.
Gold Flash(0.5u" min.) Over Nickel
G5-Gold 5u" Over Nickel
3. Applicable Wire Range: AWG#22~#28
4. Insulation O.D.: 1.45mm (Max.)
5. Current Rating: 2A AC,DC
6. Voltage Rating: 250V AC,DC
7. Temperature Rang: -25°C~+85°C
8. Contact Resistance: 20mΩ Max
9. Insulation Resistance: 1000MΩ Min
10. Withstanding Voltage: 1000V AC/minute

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 1127T 镀半金 (杜邦2.0)			
DRAWN: LYF	DATE: 2020-11-28	PART. NO.	3-2010T012-D000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-1127-0002	REV.	A XR00

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05