




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.07.31	阿 树




- Specifications
- Voltage rating:600V AC/DC
 - Current rating:9A AC/DC
 - Withstanding voltage:1500V AC/minute
 - Temperature range:-45° to+125°
 - Insulation resistance:≥1000MΩ Min
 - Contact resistance:≤10mΩ Max

PART NO.:
X9357 T F-P SN-L U
① ② ③ ④ ⑤ ⑥ ⑦


- ① Series No
② Category: T-terminal
③ Shape: F-Female
④ Material: P-Phosphor bronze
⑤ Plating style: SN-Tin Plated
⑥ Special No: L-Low foot
⑦ Type: U-upgrade version




SEC:A-A



SEC:B-B



SEC:C-C



SEC:D-D

X9357TF-PSN-LU	Phosphor Bronze AWG#26~20	X9357H
PART NO	Material	Wire Range
		Suitable XKB Housing

ANGLAR	
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿 树		MODEL TYPE: 4.20mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9357TF-PSN-LU
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1