

B



- U

Ordering Information



Pin	Type	Colour
	Y=孔座	默认=本色
	A=直针	R=红色
	AW=定位弯针	L=蓝色

1



2x2~2x3Pin





2x4Pin





2x5Pin





2x6Pin



2x7Pin




2x8Pin以上



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -40℃~ +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0(2)
PIN Brass Tin-plated

			GENEERL TOLERANCE	制 图 DRAWING	02	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL					
1	初版发行		X.XX ±0.20	比 例 SCALE		产品名称 TITLE	SPH (2.00) 双排直针 带柱 Pin 位图	版 本 REV.	A
			X.XXX ±0.10	投 影 Projection		产品料号 PART NO.	HC-SPH-2xNA	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°			材 料 MATERIAL		页 次 SHEET	2/2