




NO.	Operating Type	Part No.
1	Push To Lock	K8-8585D-L2
2	Push No Lock	K8-8585D-N2
3	Push No Sound No Lock	K8-8585D-NN2

Cover type: Outer buckle

NO.	Operating Type	Part No.
1	Push To Lock	K8-8585D-L1
2	Push No Lock	K8-8585D-N1
3	Push No Sound No Lock	K8-8585D-NNW
4	Push No Sound No Lock	K8-8585D-NN1

全黑阻燃款

⑧	Terminal	—	6	Brass strip	Plating silver	—
⑦	Contact	—	2	Phosphor bronze	Plating silver	—
⑥	Securing glue	—	2	PA66	Black	—
⑤	Spring	—	1	SUS	Natural	—
④	Base	—	1	PBT	Black	—
③	Crochet Needle	—	1	SUS	Natural	—
②	Cover	—	1	POM	Gray	—
①	KNOB	—	1	POM	White/Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS

DATE

DRAWN xu qi feng

2014.12.05

CHECKED

TITLE:

PUSHBUTTON SWITCHS

APPROVALS

PART NO.

TOLERANCES ARE

30~以上

10~30

5~10

~ 5

±0.30

±0.20

±0.15

±0.10

ANGLE

UNIT: mm

SCALE: 1:1

DRAWING NO.

PROJ:

SHEET 1 OF 1

Circuit Diagram

PCB Layout(Pattern Side)

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			