


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		INITIAL RELEASE	2024.07.13	阿 树

- SPECIFICATIONS
- Voltage rating:100VAC,DC
 - Current rating:2A,AC,DC
 - Withstanding Voltage:500V AC/minute
 - Temperature range:-25°C+85°C
 - Contact resistance:20mΩ max

PART NO.:

X 1501 T-P SN
① ② ③ ④ ⑤

- ① Series No
② Category:T-Terminal
③ Material:P-Phosphor bronze
④ Plating: SN-Tin-Plated
V01-Gold flash



SECTION A-A

SECTION B-B

SECTION C-C

SECTION D-D

X1501T-PXX	Phosphor Bronze	Tin-Plated	AWG#24~28	X1501H
PART NO	Material	Finish(pin)	Wire Range	Suitable XKB Housing

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿 树	VIEW:	MODEL TYPE: 1.5mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1501T-PSN
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1