



电路原理图

NOTES:

1. Rating: 16V DC
1. 额定值: 16V DC
2. Dielectric Strength: 250V (50Hz) AC
2. 耐电压: 250V (50Hz) AC
3. Contact Resistance: $\leq 200\text{m}\Omega$
3. 接触电阻: $\leq 200\text{m}\Omega$
4. Insulation Resistance: $\geq 50\text{M}\Omega$
4. 绝缘电阻: $\geq 50\text{M}\Omega$
5. Operating Force: $80\text{g} \pm 20\text{g}$
5. 操作力: $80\text{g} \pm 20\text{g}$
6. Life: 20,000 times
6. 寿命: 20,000 次

6	Solder foot 焊锡脚	Brass	3	Ag plating 镀银
5	Base 基座	Nylon	1	Black 黑色
4	cover 盖子	Nylon	1	Black 黑色
3	spring 弹簧	Wire	1	
2	reed 簧片	Silver coated copper	1	Ag plating 镀银
1	Press handle 按柄	POM	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP72332
DATE	2019	APPROVAL B	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			