






HAOYU



SCHEMATIC



P.C.B LAYOUT

PIN	$\phi 1.0$	$\phi 1.3$	$\phi 1.65$
APPD.			

					TOLERANCE UNLESS SPECIFIED						
					UP TO 5mm: ± 0.1	ANGULAR	A0	2018.4.4	初版	GYW	
					ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS	BY	APPD
5	DC033 PING	BRASS	1	Ni PLATED	TITLE: DC JACK			UNIT : MM	ROHS COMPLIANT	DWN	
4	DC033A 5#CURVE PIECE	BRASS	1	Ag PLATED	MODEL: DC-033A-1.0			SCALE: 6:1	CHK'D		
3	DC033A 4#FLAT PIECE	BRASS	1	Ag PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD			
2	DC033A 3#SPRING	SUS	1	Ag PLATED							
1	DC033A CASE	PBT	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING							REV :A0



HAOYU(HONGKONG)LIMITED
皓宇(香港)有限公司

PRO.AGL: REV :A0