




+

+



技术要求 Specification:

- 1、材质 Material: PA6 UI94V-2(0)
- 2、额定电流 Current rating: 3A max
- 3、额定电压 Voltage rating: 250V AC/DC
- 4、温度范围 Temperature range: 25°C to +85°C
- 5、接触电阻 Contact resistance: $\leq 20\text{m}\Omega$
- 6、绝缘电阻 Insulation resistance: $\geq 1000\text{m}\Omega$
- 7、耐压 Withstand voltage: 1000V AC/minute
- 8、适配的端子 Adaptable terminals: HX15000-P
- 9、适配的插座 Adaptable Receptacle: HX15000-R, HX15000-A/WAP/WAD/AB/AWB
- 10、塑料件表面应无明显疤痕、杂色、开裂、毛刺、飞边、缺料及影响使用的变形。 Plastic part: smooth and flat surface without discolor, broken, crack, distortion defects is acceptable.

未注公差表 TOLERANCE TABLE		设计 DRAWN BY	王鹏程 WANG PENGCHENG	产品名称 PRODUCT NAME	插座 RECEPTACLE HOUSING
≤3	±0.1	审核 CHECKED BY	郑建银 ZHENG JIANYING	产品型号 PRODUCT MODEL	ZH-2Y~15Y
≤10	±0.2	批准 APPROVED BY	沈才义 SHEN CAIYI	产品代号 PRODUCT NO	HONGXING NO
≤20	±0.3	日期 DATE	2019.09.09	HX15000-2Y~15Y	
≤40	±0.4				
≤80	±0.5				
视图 VIEW	比例 SCALE	单位 UNIT	版次 VERSION	页码 SHEET	
Φ	8:1	mm	A	1/1	浙江红星电业有限公司 Zhejiang Hongxing Electrical Co., Ltd.