





Specifications

备注 (Remark)
1. 材料 (MATERIAL)
胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.
Housing: PBT+30%G.F UL94V-0, Color: Black
四方针: 黄铜, 镍底30u"MIN, 表面镀普金
Contact: Brass, GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL
2. 特性 (characteristics):
额定电压: 250V AC/DC
Rated Voltage: 250V AC/DC
额定电流: 3 AMP
Raring Current: 3 AMP.
接触阻抗: 20 mΩ MAX.
Contact Resistance: 20 mΩ MAX.
绝缘阻抗: 1000 MΩ MIN.
Insulating Resistance: 1000 MΩ MIN.
耐电压: AC 1500V/分钟.
Withstanding Voltage: AC 1500V/minute.
温度范围: -40° C to +85° C
Temperture Range: -40° C to +85° C



Ordering Information

B190-1 XX A0 A S B E 7

NO OF PINS	Contact Plating	INSULATOR	B Back	PACKING
6-64P	Full of Gold	Semi-gold	MATERIAL:	
A0=0.8u"	B0=0.8u"	A: PBT	G Grey427	A: PE Bag
A1=1u"	B1=1u"	B: PA6T	E: Grey413	B: Tape & Reel
A2=1.5u"	B2=1.5u"	C: PA9T	W White	C: Tube
A3=2u"	B3=2u"	D: LCP	U: Blue	D: Tube+CAP
A4=3u"	B4=3u"			E: Tray
A5=5u"	B5=5u"			
A6=10u"	B6=10u"			
A7=15u"	B7=15u"			
A8=20u"	B8=20u"			
A9=30u"	B9=30u"			
S1=Ordinary Tin Plated				
S2=Matte Tin Plated				
S3=Tin-plated High-temperature				

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司			
				X.X	±0.25	UNIT		MM		Dongguan Yuxi Electronic Co., Ltd.			
				X.XX	±0.20	SIZE	A4	DESIGN	李官森2022.05.25	PART NO	B190-1XXA0ASBE7		
				X.XXX	±0.10	SHEET	1/1	CHECK		TITLE	2.54简半 塑高9.0 XXP 镀普金 PBT		
				Angle	±3°	PROJ.	1/1	APPROVE			180度 L=11.6/3.3 盒装		
				DIM	TOL					Custoner No.			