

[illegible]

11	12	13	14	15
变更单号	版本	日期	内容描述	变更者

孔数	A	B
2	3.96	7.92
3	7.92	11.88
4	11.88	15.84
5	15.84	19.80
6	19.80	23.76
7	23.76	27.72
8	27.72	31.68
9	31.68	35.64
10	35.64	39.60
11	39.6	43.56
12	43.56	47.52

技术参数:

- 额定电流:7A AC/DC.
- 额定电压:250V AC/DC.
- 工作温度:-20℃ to 85℃.
- 接触电阻:20mΩ Max.
- 绝缘电阻:1000MΩ Min.
- 耐电压:1000V AC/minute.
- 符合ROSH要求.

材料

- 基座:PA66.
- 插针:黄铜.
- 电镀:镍 和 锡.

PCB寸法


CAX 浙江创都电子科技有限公司
ZHEJIANG CHUANGDU ELECTRONICS AND TECHNOLOGY CO.,LTD.

X. ±0.50	设计	叶云龙	日期	2020.11.05	名称	VH-AW 240°				
X.X ±0.25	审核	黄斌斌	日期	2020.11.05						
X.XX ±0.20	批准	王红芳	日期	2020.11.05	料号					
X° ±3°										
未注公差	比例	1:1	单位	mm	版本	A	页码	1 OF 1	A4	

- [illegible]

[illegible]

- [illegible]

[illegible]

11	12	13	14	15
变更单号	版本	日期	内容描述	变更者

The diagram illustrates the mechanical specifications of a PCB component through three distinct views:

- Top View:** Shows four mounting pins spaced at distance A ± 0.05 mm. The overall width is B ± 0.2 mm. A dimension of 3.2 ± 0.2 mm is indicated for one of the pin bases.
- Side View:** Shows the profile of the component with a total height of 9.4 ± 0.2 mm. The base width is divided into two sections: 7.7 ± 0.2 mm and 3.5 ± 0.2 mm.
- Bottom View:** Shows the underside of the component with a central width of 6.7 mm. It also indicates a pitch of 3.96 mm between the circular pad centers.

A separate section labeled "PCB寸法" shows the standard circular pad layout with a center-to-center distance of A and a specific pad diameter of 3.96 mm.

技术参数:

- 1. 额定电流: 7A AC/DC.
- 2. 额定电压: 250V AC/DC.
- 3. 工作温度: -20℃ to 85℃.
- 4. 接触电阻: 20m Ω Max.
- 5. 绝缘电阻: 1000M Ω Min.
- 6. 耐电压: 1000V AC/minute.
- 7. 符合ROSH要求.

材料

- 1. 基座: PA66.
- 2. 插针: 黄铜.
- 3. 电镀: 镍 和 锡.

孔数	A	B
2	3.96	7.92
3	7.92	11.88
4	11.88	15.84
5	15.84	19.80
6	19.80	23.76
7	23.76	27.72
8	27.72	31.68
9	31.68	35.64
10	35.64	39.60
11	39.6	43.56
12	43.56	47.52

CAX 浙江创都电子科技有限公司
ZHEJIANG CHUANGDU ELECTRONICS AND TECHNOLOGY CO., LTD.

X. ±0.50	设计	叶云龙	日期	2020.11.05	名称	VH-AW 240°
X.X ±0.25	审核	黄斌斌	日期	2020.11.05	料号	
X.XX ±0.20	批准	王红芳	日期	2020.11.05		
X° ±3°	比例	1:1	单位	m m	版本	A
未注公差	比例	1:1	单位	m m	版本	A
					页码	1 OF 1
						A4

[illegible]