




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		额定电流变更, 图面升级整理图面	2024.9.27	阿树






- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:2A AC/DC
 - Withstanding Voltage:800V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤20mΩ

PART NO.:

X2011 H F-XX A-N0
① ② ③ ④ ⑤ ⑥


- ①Series No
②Category:H-HSG
③Category:F-Female Housing
④Row No.Pin No:XX-02~15Pin
⑤Plug the Pin &Special No.:A-No Lock
⑥Material:N0-PA66 UL94V-0



A-A

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	5.98	09	16.00	19.98
03	4.00	7.98	10	18.00	21.98
04	6.00	9.98	11	20.00	23.98
05	8.00	11.98	12	22.00	25.98
06	10.00	13.98	13	24.00	27.98
07	12.00	15.98	14	26.00	29.98
08	14.00	17.98	15	28.00	31.98

Circuit 1



X2011HF-XXA-N0	PA66	X2011W	X2011TM
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X2011HF-XXA-N0
APPROVED		SIZE:	A4	DWG NO.:	