

Ordering Information

P125-12 16 A0 A S 116 A 1

备注(Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing:PA9T+30%G. F UL94V-0, Color:Black

四方针：黄铜，镍底30u"，表面镀普金

Contact:Brass, GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.




Withstanding Voltage:AC 500V/Minute.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40°C to $+105^{\circ}\text{C}$



Recommended P. C. B LAYOUT
General Tolerance ± 0.05

RoHS
COMPLIANT

客编：

注意事项

1. 带序号为必检尺寸
2. 带*为重点检验尺寸

				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE		A4	DESIGN	李青杰2023.10.19	PART NO.	P125-1216A0AS116A1
				X.XXX	±0.10							
A0	2023.10.19	/	新版发行	Angle	±3°	SHEET		1/1	CHECK		TITLE	2.54排针 2*16P L=11.6/3.0 180度 PA9T料 镀金片 袋装
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.			APPROVE		Customer No.	