




RECOMMENDED P.C.B LAYOUT (TOP VIEW)



SPECIFICATION
MATERIAL & FINISHES
 INSULATOR: PBT GLASS FILLED UL94V-0
 CONTACT: BRASS
 SHELL : STEEL
 PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL
 Operation voltage: 250 VAC max.
 Current rating: 3 Amps max.
 Contact resistance: 15 mohms max.
 Insulation resistance: 3000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1000 VAC / minute
 Operating temperature: -55°C TO +105°C



APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DMSC-9S 母头 直插 车针 全金 铆合锁螺丝			
DRAWN:	DATE:	PART. NO.	D-DMSC09PF-F001	UNIT	mm
L.YF	2018-04-07	FILE NO.	Ckmtw-DMSC-0006	SCALE	free
				REV.	A
TOLERANCE TABLE		.0	±0.30	.00	±0.20
		.000	±0.05		