





NOTES:

- 1.Rating:0.1A
1.额定值: 0.1A
- 2.Dielectric Strength: AC100V 50Hz
2.耐电压: AC100V 50Hz
- 3.Contact Resistance: $\leq 80\text{m}\Omega$ Max
3.接触电阻: $\leq 80\text{m}\Omega$
- 4.Insulation Resistance: $\geq 100\text{M}\Omega$
4.绝缘电阻: $\geq 100\text{M}\Omega$
- 5.Operating Force: $260\pm 50\text{gf}$
4- $150\pm 50\text{gf}$
- 5.操作力: $260\pm 50\text{gf}$
4- $150\pm 50\text{gf}$
- 6.Life: 50,000 times
6.寿命: 50,000 次
- 7.Temperature Range: -25°C TO $+70^{\circ}\text{C}$
7.工作温度范围: -25°C TO $+70^{\circ}\text{C}$



	1	2	3	4	5	6
F1	●			●		
F2	●	●				
F3	●					●
F4	●				●	
F5	●	●				

6	Terminal 端子	Phosphorous copper	6	Ag plating White 镀银 白色
5	Pedestal 基座	LCP	1	Black 黑色
4	Contact spring 接触簧片	SUS	5	Ag plating 镀银
3	Cover plate 盖板	SUS	1	White 白色
2	Sheath 护套	LCP	1	Black 黑色
1	Button 按钮	Reinforced nylon	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN
MODEL NO: TP-0209-4			
Https: www.rocpcu.tw			
ROPCU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			