

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 磷铜, 镍底30u", 表面镀普金

Contact: Phosphor, GOLD PLATING OVER ALL
30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 1 AMP

Rated Current: 1 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.



温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Recommended P.C.B LAYOUT

General Tolerance ± 0.05



Ordering Information

F343-12 06 A0 C MU B 4

NO. OF PINS
PER ROW
2-50P

Contact Plating
Full of Gold
A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

INSULATOR MATERIAL:
B: PA6T
C: PA9T
D: LCP
S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

客编:

注意事项

- 带序号为必检尺寸
- 带*为重点检验尺寸
- 保持力为0.3kg

OPERATION

X.X ± 0.25

X.XX ± 0.20

X.XXX ± 0.10

Angle $\pm 3^\circ$

DIM TOL

SCALE

UNIT

SIZE

SHEET

PROJ.

Fit

MM

DESIGN

CHECK

APPROVE

Yxcon

www.yxcon.com

东莞市宇熙精密连接器有限公司

Dongguan Yuxi Electronic Co., Ltd.

伍思远2023.09.18

PART NO

F343-1206AOCMUB4

1.27排母 4.3mm塑高 2*6P SMT

带内柱 U型 PA9T料 镀普金 麦拉+1000/卷

Customer No.

MODIFICATION DESCRIPTION

REV DATE SYMBOL

A0 2023.09.18 /

新版发行