

A




B

C

D





E

F



修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	黄艳兰	2021-05-10

Specifications:
 Poles: 02 to 16
 Contact resistance: $\leq 20m\Omega$
 Insulation resistance: $\geq 500M\Omega$
 Rated voltage: 100V AC DC
 Rated current: 2.0A AC DC
 Withstand Voltage: 500V AC/minute
 Temperature Range: -25°C ~ +85°C
 Housing: PA9T UL94V-0, Natural
 Contacts: PhosphorBronze / Sn-plated
 Solder tabs: Brass / Sn-plated



包装数量：每盘装800PCS。



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co., LTD

TEL : 0755-27111225 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				APPD: 核准:	TITLE: 产品名称: ZE1.5卧贴		
X.X	± 0.30	$X.X^\circ$	$\pm 3^\circ$	谢亮	PART NO: 产品编号:	HDGC1501WRD-S-XP	
X.XX	± 0.30	$X.XX^\circ$	$\pm 2^\circ$	王建业	DATE		
X.XXX	± 0.10	$X.XXX^\circ$	$\pm 1^\circ$	黄艳兰	SCALE	mm	
				DRAW: 绘图:	CODE NUMBER	A018	
				2021-05-10	1:1		